

GOIN International Vietnam Co., Ltd. Tel.:

R204, NC Building, No. 80, Ha Dac St., District 12, HCM City Tax-Code: 0314463947 Tel.: (+84) 862575751 E-mail:<u>tony.nguyen@goin-mail.com</u> Web: <u>www.goin-vn.com</u>



Puncture Strength Tester

This testing machine measures the *piercing strength* required for a needle to penetrate a sample. It is to measure rupture strength by *applying a vertical force*, used for testing physical properties of battery separators.

The NDG5 can be used to evaluate the strength of film inside lithium-ion batteries (separators) and to measure the strength required to pierce packaging materials such as food packaging films.

Measurement Examples Strength evaluation for separators inside lithium-ion batteries Piercing strength evaluation for food packaging films







FEATURE

Specialized needle


Designed with separator measurement in mind (size: ø1, 0.5R tip shape)



* The photo shows a needle with a holder. Holder is not included in a single needle purchase.



SYSTEM CONFIGURATION DIAGRAM / MEASUREMENT DATA



NDG5 Puncture Strength Tester

Dimensions/Weight (approx.)	Measuring unit: W230 × D230 × H460 (mm) / 13 kg Amplifier: W180 × D400 × H400 (mm) / 13 kg
Power source	100 VAC, power consumption: 20 W Max.
Measurement environment temperature and humidity	20 to 30°C / 50 to 70 % RH. (No condensation.) Temperature and humidity should be kept constant during measurement. (Standard temperature and humidity conditions: 20°C / 65% RH) *The instrument should be located to minimize influence from wind or vibrations.
Load detection	Detector: Ring-type detector with differential transformer Load (full scale): Switchable between 4 ranges (100 gf, 200 gf, 500 gf, 1000 gf) Accuracy: $\pm 0.5\%$ or less of full scale
Displacement detection	Detector: Potentiometer Displacement quantity: Max. 20 mm Accuracy: ±1% or less of full scale

Needle diameter	1.0 mm
Sample diameter after setting the sample	10 mm
Displacement rate	Standard measurement: 0.02 mm/sec <1 mm/50 sec> High-sensitivity measurement: 0.0067 mm/sec <1 mm/150 sec> Other rates can be specified by settings.
Measuring movement	Load control system Displacement control system The above 2 systems are switchable
Sample size	Dimensions: 15 x 15 mm (min.) Thickness: 1mm (max.)

▲ Precaution For safety use, please read the operation manual / the instruction carefully and throughly before using the tester.

Specification details recorded here are subject to change without notice. We appreciate your understanding.



E-mail: tony.nguyen@goin-mail.com Web: www.goin-vn.com

(+84) 862575751

Tax-Code: 0314463947